


dametric 

# AGS-SP-IZ-H

## DESCRIPTION



# HOLDER PART TO THE AGS-IZ SENSOR

## CONTENT

1	GENERAL.....	2
2	SEALING .....	2
3	MOUNTING.....	2
4	OUTLINE DRAWING .....	3
5	METSO PAPER PART NO .....	3
6	CONTACTS .....	3

## 1 GENERAL

The holder part of the AGS will mechanically fit the AGS-house to the refiner stator plate.

There are several types of holders for different lengths, threads and sealing.

The AGS-SP-IZ-H will fit the flat zone AGS in a Valmet RLP-70 CD and the RGP-60 SD refiners.

The holder is included in a new AGS sensor but can also be bought as a spare part. The holder is replaced if the thread is destroyed, if the sealing surface is uneven or if the contact surface to the segment plate is bad.

## 2 SEALING

This type of holder includes a Shamban type sealing, SHAMBAN (Dametric art. no.) or M-604910 (Valmet art. no.).

## 3 MOUNTING


The holder is mounted direct to the AGS house (AGD-HM3) and the sensor tip must be mounted afterwards.

Unscrew the locking nut, mount the holder and then put the locking nut back on again.

The locking nut shall not be tightened yet; this to assure that the holder can be rotated when mounting the AGS sensor to the refiner.

Tight the locking nut when the AGS sensor is tightened toward the refiner plates.

## 4 OUTLINE DRAWING



## 5 VALMET PART NO

Valmet part no.: VAL0243455.

## 6 CONTACT

Sales, development, production and service:

### Dametric AB

Jägerhorns Väg 19, 141 75 Kungens Kurva, Sweden

Phone: +46-8 556 477 00

Telefax: +46-8 556 477 29

e-mail: [ags@dametric.se](mailto:ags@dametric.se)

Web site: [www.dametric.se](http://www.dametric.se)

Development, production and service:

dametric 

Valmet 